

CONNECT

Draka 1U 24port Cat5e UTP 180° Punch down Panel



Cat5e Unshielded 24-Port Punch Down Patch Panel

- Cat5e compliant performance
- 180° termination blocks for easy termination
- Compatible with 110 & Krone Punch Tools
- Lasermark labels available on request

Specification



Description

JAI DE

Panel SPCC, 1.2 mm thickness

RJ45 jack contact material and finish Phosphor Bronze

Contact area: Min 3 mm 50 micro-inch Gold

plated over Nickel colour

IDC terminal and finish

Phosphor Bronze with min, 50 micro-inch Tin

plated

Wire size compatibility 23-26 AWG solid wire

Dimensions (WxHxD)mm 482 x 44 x 93

Performance

Item

IDC cap colour code supports both wiring

schemes TIA 568A & 568B

Insertion force 20N max

Retention strength 7.7kg between jack and plug

Operating temperature -10°C to 60°C

Durability Jack 750 cycles







UCCONNECT

Draka 1U 24port Cat5e UTP 180° Punch down Panel

Construction





Technical data

Mate	rial Code	Material Description	Description Code	Weight	Items per Packaging Unit	
1021280	YPWBP00105	1U 24port Cat5e UTP 180° Punchdown Panel in Black	UC C300 PW TR U BK 24 1U	545g	1 or 20	
Related Products						
Mate	rial Code	Material Description	Description Code	Weight	Items per Packaging Unit	
1021314	YSBBP00119	Support bar for 180° Patch Panel	UC CACC SB	267g	1 or 20	

© PRYSMIAN GROUP 2013, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.