

Type Approval Certificate



This is to certify that the undernoted product(s) has/have been tested in accordance with the relevant requirements of the GL Type Approval System.

Certificate No. **33 776 - 06 HH**

RG223 / 2YCCY 0.89s/2.95Ds

Inner conductor: Copper wire, silver plated 0,90 mm
Insulation: PE; 2,95 mm
1. Braid: Copper wire braid silver plated
2. Braid: Copper wire braid silver plated
Sheath: PVC

Electrical properties: Mutual capacitance: 100 pF/m
Impedance: 50 Ohm
Max. operating frequ.: 12,4 GHz
Operating voltage: 1,4 kV rms

Mechanical properties: Operating temp.: -40°C to 85°C
Bending radius: 5 x outer diameter (without load)

Place of production: Draka Comteq / Cable Solutions EMEA, Wohlauer Str. 15, D-90475 Nürnberg

Valid until **2017-01-10**

Page **2 of 2**

File No. **I.N.01**

Hamburg, 2012-01-10

Type Approval Symbol



Germanischer Lloyd


Christoph Kutzner


Carsten Hunsalz