

Datacom Connectivity

1U 24 Port LC/SC MM Patch Panel Black

Issue date: 8-Feb-11

Supersedes: - -

Page: 1/3




Value Innovation is a way of looking at the world. By combining market insight with technological know-how and building strong, long-lasting relationships, we add value to your business with advanced communication solutions and services that are designed to last. No matter how complex your challenge, we have a product or solution that will do more than meet your needs. New applications, breakthrough cables or complete network designs - it's all part of what we call Value Innovation, and it's what drives us.

#### MM Patch Panels compatible with UC<sup>Connect</sup> system

- Available with LC/SC Connectors
- Optimised design for easy fibre management
- Can be installed in majority of racks and wall mounted enclosures
- Cable Management supplied as standard



Specification	
Item	Description
1 Dust Cover	PVC
2 Matrix	Steel, Thickness: 1.2mm
3 Ledger Plate	Steel, Thickness: 2mm
4 Splice Tray	ABS + PC
5 Panel	Steel, Thickness: 1.2mm
6 Plastic Lock	ABS
7 Adaptor	12 LC/SC Duplex
Performance	
Dimension	44.5 x 480.4 x 280mm
Weight	3.5kg
Surface Finish	Powder Coating





#### Technical data

Material code	SAP Description	Material Description
1023600	UC COMF PP LD SO BK 24 1U	1U 24 Port LC Duplex Multimode Patch Panel Black
1023601	UC COMF PP LD SO BK 12 1U	1U 12 Port LC Duplex Multimode Patch Panel Black
1023610	UC COMF PP SD SO BK 24 1U	1U 24 Port SC Duplex Multimode Panel Black
1023611	UC COMF PP SD SO BK 12 1U	1U 12 Port SC Duplex Multimode Panel Black
1023700	UC COSF PP LD SO BK 24 1U	1U 24 Port LC Duplex Single mode Panel Black

#### Related Products

1023200-00100CM	UCCOM4 PT LC R AQ 00100	LC OM4 50/125 Pigtail 1m
1023210-00100CM	UCCOM4 PT SC R AQ 00100	SC OM4 50/125 Pigtail 1m
1023220-00100CM	UCCOM4 PT ST R AQ 00100	ST OM4 50/125 Pigtail 1m
1023400-00100CM	UC COM4 PC LC R AQ 00100	LC - LC Duplex 50/125 OM4 Patchcord 1m
1023401-00100CM	UC COM4 PC LC SC AQ 00100	LC - SC Duplex 50/125 OM4 Patchcord 1m
1023402-00100CM	UC COM4 PC LC ST AQ 00100	LC - ST Duplex 50/125 OM4 Patchcord 1m
1023400-00200CM	UC COM4 PC LC R AQ 00200	LC - LC Duplex 50/125 OM4 Patchcord 2m
1023401-00200CM	UC COM4 PC LC SC AQ 00200	LC - SC Duplex 50/125 OM4 Patchcord 2m
1023402-00200CM	UC COM4 PC LC ST AQ 00200	LC - ST Duplex 50/125 OM4 Patchcord 2m
1023400-00300CM	UC COM4 PC LC R AQ 00300	LC - LC Duplex 50/125 OM4 Patchcord 3m
1023401-00300CM	UC COM4 PC LC SC AQ 00300	LC - SC Duplex 50/125 OM4 Patchcord 3m
1023402-00300CM	UC COM4 PC LC ST AQ 00300	LC - ST Duplex 50/125 OM4 Patchcord 3m