

Prysmian

10 YEAR

EXTENDED
WARRANTY

Cables and Components Selector chart

Cable	Cores	Conductor	BW	BW LSF	CW	CW LSF	A1/A2	E1W	E1W LSF	Telcleat	Telcleat LSOH	Claw Cleat Al	Claw cleat Fe
BS 5467	3	1.5	KA410-52	-	KA419-52	-	-	KAA413-71	-	385AA01	-	370BA01	-
BS 5467	3	2.5	KA410-52	-	KA419-52	-	-	KAA413-52	-	385AA01	-	370BA02	-
BS 5467	3	4	KA410-52	-	KA419-52	-	-	KAA413-52	-	385AA02	-	370BA02	-
BS 5467	3	6	KA410-53	-	KA419-53	-	-	KAA413-52	-	385AA02	-	370BA02	-
BS 5467	3	10	KA410-53	-	KA419-53	-	-	KAA413-53	-	385AA03	-	370BA03	-
BS 5467	3	16	KA410-55	-	KA419-55	-	-	KAA413-55	-	385AA04	-	370BA04	-
BS 5467	3	25	KA410-55	-	KA419-55	-	-	KAA413-55	-	385AA05	-	370BA06	-
BS 5467	3	35	KA410-56	-	KA419-56	-	-	KAA413-56	-	385AA05	-	370BA06	-
BS 5467	4	1.5	KA410-52	-	KA419-52	-	-	KAA413-71	-	385AA01	-	370BA01	-
BS 5467	4	2.5	KA410-52	-	KA419-52	-	-	KAA413-52	-	385AA01	-	370BA02	-
BS 5467	4	4	KA410-52	-	KA419-52	-	-	KAA413-52	-	385AA02	-	370BA02	-
BS 5467	4	6	KA410-53	-	KA419-53	-	-	KAA413-53	-	385AA03	-	370BA03	-
BS 5467	4	10	KA410-55	-	KA419-55	-	-	KAA413-55	-	385AA04	-	370BA04	-
BS 5467	4	16	KA410-55	-	KA419-55	-	-	KAA413-55	-	385AA04	-	370BA05	-
BS 5467	4	25	KA410-56	-	KA419-56	-	-	KAA413-56	-	385AA05	-	370BA06	-
BS 5467	4	35	KA410-56	-	KA419-56	-	-	KAA413-56	-	385AA06	-	370BA06	-
BS 6724	3	1.5	-	420LSF-52	-	422LSF-52	-	-	421LSF-71	-	385LSF01	370BA01	-
BS 6724	3	2.5	-	420LSF-52	-	422LSF-52	-	-	421LSF-71	-	385LSF01	370BA01	-
BS 6724	3	4	-	420LSF-52	-	422LSF-52	-	-	421LSF-52	-	385LSF02	370BA02	-
BS 6724	3	6	-	420LSF-52	-	422LSF-52	-	-	421LSF-52	-	385LSF02	370BA02	-
BS 6724	3	10	-	420LSF-53	-	422LSF-53	-	-	421LSF-53	-	385LSF03	370BA03	-
BS 6724	3	16	-	420LSF-55	-	422LSF-55	-	-	421LSF-55	-	385LSF04	370BA04	-
BS 6724	3	25	-	420LSF-55	-	422LSF-55	-	-	421LSF-55	-	385LSF05	370BA06	-
BS 6724	3	35	-	420LSF-56	-	422LSF-56	-	-	421LSF-56	-	385LSF05	370BA06	-
BS 6724	4	1.5	-	420LSF-52	-	422LSF-52	-	-	421LSF-71	-	385LSF01	370BA01	-
BS 6724	4	2.5	-	420LSF-52	-	422LSF-52	-	-	421LSF-52	-	385LSF01	370BA02	-
BS 6724	4	4	-	420LSF-52	-	422LSF-52	-	-	421LSF-52	-	385LSF02	370BA02	-
BS 6724	4	6	-	420LSF-53	-	422LSF-53	-	-	421LSF-53	-	385LSF03	370BA03	-
BS 6724	4	10	-	420LSF-55	-	422LSF-55	-	-	421LSF-55	-	385LSF04	370BA04	-
BS 6724	4	16	-	420LSF-55	-	422LSF-55	-	-	421LSF-55	-	385LSF04	370BA04	-
BS 6724	4	25	-	420LSF-56	-	422LSF-56	-	-	421LSF-56	-	385LSF05	370BA06	-
BS 6724	4	35	-	420LSF-56	-	422LSF-56	-	-	421LSF-56	-	385LSF06	370BA06	-
BS 6724	5	1.5	-	420LSF-52	-	422LSF-52	-	-	421LSF-52	-	385LSF02	370BA02	-
BS 6724	5	2.5	-	420LSF-53	-	422LSF-53	-	-	-	-	385LSF03	370BA03	-
BS 6724	5	4	-	420LSF-53	-	422LSF-53	-	-	421LSF-53	-	385LSF03	370BA03	-
BS 6724	5	6	-	420LSF-55	-	422LSF-55	-	-	421LSF-55	-	385LSF04	370BA04	-
BS 6724	5	10	-	420LSF-55	-	422LSF-55	-	-	421LSF-55	-	385LSF05	370BA05	-
BS 6724	5	16	-	420LSF-56	-	422LSF-56	-	-	421LSF-55	-	385LSF05	370BA06	-
BS 6724	7	1.5	-	420LSF-53	-	422LSF-53	-	-	-	-	385LSF03	370BA02	-
FP600s	3	4	-	-	-	422LSF-55	-	-	421LSF-55	-	-	-	370CG-04
FP600s	3	6	-	-	-	422LSF-55	-	-	421LSF-55	-	-	-	370CG-04
FP600s	3	10	-	-	-	422LSF-55	-	-	421LSF-55	-	-	-	370CG-05
FP600s	3	16	-	-	-	422LSF-55	-	-	421LSF-55	-	-	-	370CG-05
FP600s	3	25	-	-	-	422LSF-56	-	-	421LSF-56	-	-	-	370CG-06
FP600s	3	35	-	-	-	422LSF-56	-	-	421LSF-56	-	-	-	370CG-07
FP600s	3	50	-	-	-	422LSF-56	-	-	421LSF-56	-	-	-	370CG-07
FP600s	4	4	-	-	-	422LSF-55	-	-	421LSF-55	-	-	-	370CG-04
FP600s	4	6	-	-	-	422LSF-55	-	-	421LSF-55	-	-	-	370CG-05
FP600s	4	10	-	-	-	422LSF-55	-	-	421LSF-55	-	-	-	370CG-06
FP600s	4	16	-	-	-	KA493-56	-	-	KA493-56	-	-	-	370CG-06
FP600s	4	25	-	-	-	422LSF-56	-	-	421LSF-56	-	-	-	370CG-07
FP600s	4	35	-	-	-	422LSF-57	-	-	421LSF-57	-	-	-	370CG-07
FP600s	4	50	-	-	-	422LSF-57	-	-	421LSF-57	-	-	-	370CG-07
FP500	3	1.5	-	-	-	422LSF-52	-	-	421LSF-52	-	-	-	370CG-02
FP500	3	2.5	-	-	-	422LSF-53	-	-	421LSF-52	-	-	-	370CG-02
FP500	4	1.5	-	-	-	422LSF-52	-	-	421LSF-52	-	-	-	370CG-02
FP500	4	2.5	-	-	-	422LSF-53	-	-	421LSF-53	-	-	-	370CG-03
PRY EV (Non SWA)	3	4	-	-	-	-	KM409-55	-	-	385AA03	-	370BA03	-
PRY EV (Non SWA)	3	6	-	-	-	-	KM409-55	-	-	385AA03	-	370BA03	-
PRY EV (SWA)	3	4	KA410-53	-	KA419-53	-	-	KAA413-53	-	385AA04	-	370BA04	-
PRY EV (SWA)	3	6	KA410-55	-	KA419-55	-	-	KAA413-55	-	385AA04	-	370BA05	-