

# UC<sup>CONNECT</sup>

## 2U 48port Cat5e UTP 180° Punch Down Patch Panel



### Cat5e Unshielded 48-Port Punch Down Patch Panel

- Cat5e compliant performance
- 180° termination blocks for easy termination
- Compatible with 110 & Krone Punch Tools
- Lasemark labels available on request

## Specification




Item	Description
Panel	SPCC, 1.5mm thickness
RJ45 jack contact material and finish	Phosphor Bronze  Contact area : Min 3 mm 50 micro-inch Gold plated over Nickel colour
IDC terminal and finish	Phosphor Bronze with min, 50 micro-inch Tin plated
Wire size compatibility	23-26 AWG solid wire
Dimensions (WxHxD) mm	482 x 88 x 29
<b>Performance</b>	
IDC cap colour code supports both wiring schemes TIA 568A & 568B	
Insertion force	20N max
Retention strength	7.7kg between jack and plug
Operating temperature	-10°C to 60°C
Durability	Jack 750 cycles

# UC<sup>CONNECT</sup>

## 2U 48port Cat5e UTP 180° Punch Down Patch Panel

### Construction



### Technical data

Material Code	Material Description	Description Code	Weight	Items per Packaging Unit
1021283	YPWBP00108 2U 48port Cat5e UTP 180° Punchdown Panel in Black	UC C300 PW TR U BK 48 2U	985g	1 or 20
<b>Related Products</b>				
Material Code	Material Description	Description Code	Weight	Items per Packaging Unit
1021314	YSBBP00119 Support bar for 180° Patch Panel	UC CACC SB	267g	1 or 20

© PRYSMIAN GROUP 2013, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.