

UC^{CONNECT} Category 6 Shielded Tool-Less 180° Keystone Jack



Cat6 Shielded Tool-Less Keystone Jack


- Rugged die cast housing to ensure ultimate electromagnetic shielding performance
- Cat6 compliant performance
- Easy install facilitated by tool free wire termination
- Fully compatible with our full range of faceplates, adapters and boxes
- Fits into 32 mm back-box with angled adapter
- Also available as UC^{Precon} pre-terminated cabling solution
- Available in Black, Grey, Red, White, Yellow, Blue, Green.

Specification



Item	Description
Shield	Nickel plated bronze
RJ45 Plastic housing	ABS + PC
RJ45 jack contact material and finish	Phosphor Bronze Contact area : Min 3 mm 50 micro-inch Gold plated over Nickel colour
IDC terminal and finish	Phosphor Bronze with min, 50 micro-inch Tin plated
Wire size compatibility	23-26 AWG solid wire
Housing	Zinc die cast Nickel plating
Dimensions	41mm x 24mm x 18mm
Performance	
IDC cap colour code supports both wiring schemes TIA 568A & 568B	
Insertion force	900 gm for 8 contacts
Retention strength	7.7kg between jack and plug
Operating temperature	-40°C to 80°C
Durability	Jack 750 cycles

UC^{CONNECT} Category 6 Shielded Tool-Less 180° Keystone Jack Construction



Technical data

Material Code	Material Description	Description Code	Weight	Items per Packaging Unit
1021261	YMJB00096 Cat.6 FTP Keystone Jack 180° Toolless in Silver	UC C400 MJ TF S	11,7g	1 or 50
Related Products				
Material Code	Material Description	Description Code	Weight	Items per Packaging Unit
1021310	YPPBP00116 1U 24port FTP Cat6 Keystone Panel with Rear Management in Black	UC C400 PP S BK 24 1U	720g	1 or 15
1021333	YAABP00127 Angled Single Port Adaptor 25 X 50	UC CACC AA 01 EU	8g	1 or 50
1021337	YMABP00131 LI6C Flat Single Adaptor 38 X 25	UC CACC MA 01 6C	8g	1 or 50
1021338	YAABP00132 LI6C Angled Single Adaptor 38 x 25	UC CACC AA 01 6C	8g	1 or 50
1021329	YMABP00123 Flat Single Adaptor 25 x 50	UC CACC MA 01 EU	8g	1 or 50

© PRYSMIAN GROUP 2013, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.