


# UC400 S23 U/FTP Cat.6 PE

## U/FTP



## Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)  
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T; 10GBase-T  
IEEE 802.5 16 MB; ISDN; FDDI; ATM

## Standards

EIA/TIA-568-B.2-10 Draft 5.0  
ISO/IEC 11801 2<sup>nd</sup> ed.  
EN 50173-1  
EN 50288-10 Draft  
IEC 61156-5 (46C/783/CDV)

## Construction

Conductor	bare copper wire, Ø 0.56 mm (AWG23)
Insulation	Foamskin Polyethylene, Ø 1.35 mm
Twisting	2 cores to the pair
Pair screen	<b>High Performance STP:</b> Al-laminated plastic foil, patented wrapping of two pairs each, drain wire AWG26 tinned
Cable lay up	2x2 pairs to the core
Sheath	PE, black, for outdoor installation

## Mechanical properties

Bending radius	Installation	8 x Outer diameter
	Installed	4 x Outer diameter
Temperature range	During operation	-20°C to + 60°C
	During installation	0°C to + 50°C

## UC400 S23 U/FTP Cat.6 PE

### Electrical properties

at 20°C ± 5°C

Loop resistance		≤ 176 Ω /km
Resistance unbalance		≤ 2%
Insulation resistance	(500 V)	≥ 2000 MΩ *km
Mutual capacitance	at 800 Hz	Nom. 43 nF/km
Capacitance unbalance	(pair/ground)	≤ 1500 pF/km
Mean characteristic impedance	100 MHz	100 ± 5Ω
Nominal velocity of propagation		Ca. 79 %
Propagation delay	Nominal	Nom. 450 ns/100m
Delay skew	Nominal	Nom. 15 ns/100m
Test voltage	(DC, 1 min) core/ core and core/screen	1000 V
Transfer impedance	at 1 MHz	≤ 50 mΩ /m
	at 10 MHz	≤ 100 mΩ /m
	at 30 MHz	≤ 200 mΩ /m
	at 100MHz	≤ 1000 mΩ /m

### Electrical data (nominal)

acc. to Cat.6 (at 20°C)

F (MHZ)	Attenuation (dB/100m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100m)	PS-ACR (dB/100m)	ELFEXT (dB/100m)	PS-ELFEXT (dB/100m)	Return loss (dB)
1.0	1.8	100	97	98	95	105	105	-
4.0	3.4	100	97	97	94	105	102	27
10.0	5.4	100	97	95	92	97	94	30
16.0	6.8	100	97	93	90	93	90	30
20.0	7.7	100	97	92	89	91	88	30
31.2	9.6	100	97	90	87	87	84	30
62.5	13.7	100	97	86	83	81	78	30
100.0	17.4	100	97	83	80	77	74	30
125.0	19.5	95	92	75	72	75	72	26
155.5	21.9	94	91	72	69	73	70	26
175.0	23.3	93	90	70	67	72	69	25
200.0	25.0	92	89	67	64	71	68	25
250.0	28.1	90	87	62	59	69	66	24
300.0	30.9	89	86	58	55	67	64	24
400.0	38.3	87	84	48	45	64	61	23

## UC400 S23 U/FTP Cat.6 PE

### Technical data

Product code	Cable type	Brand name	Outer diameter	Weight	Copper content	Tensile force
			Mm			kg/km
1027713	J-02YS(St)2Y 4x2x0.56	UC400 S23 Cat.6 S/FTP PE 4P	8.6	62	24	80

### Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
UC400 S23 C6 U/FTP 4P PE 1000DW	1027713-01000DW	60011456	60011455
UC400 S23 C6 U/FTP 4P PE		60011456	60011456

© PRYSMIAN GROUP 2011, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.