


CasaLink Block Terminal (CBT) Drop Cables

Product code – See tables below

TV06051



-not to scale-

Cable Design

According to IEC/EN 60794

- **Optical Fibre:** 250µm single-mode.
- **Tube:** thermoplastic material, containing between 1 and 24 single-mode optical fibres and filled with a suitable water tightness compound.
- **Strength Member:** 3 x 0.32mm brass plated steel wires.
- **Longitudinal Water Tightness:** water swellable materials (core only).
- **Outer Sheath:** UV resistant HDPE.
- **Grooves/Stripes:** Indicate planes for easy sheath removal.

Cable Application

This loose tube optical drop cable is design for aerial and/or duct applications and is suitable for use under 11 kV power cables. Please refer to our General Installation (Datasheet Ref: CIG059) and Safety & Handling recommendations (Generic Optical cable MSDS - Datasheet Ref: 9980-02-1) before handling.

Cable is suitable for Openreach PIA approval when tested together with tension clamps from PLP Preformed Line Products (item code FODE 5709060R) and fibre locking bollards from OPT Services Ltd (item code T0218).

Technical Data


No. of Fibres		1	2	4	8	12	24
Layout	-	Single central tube					
Unit Diameter – Ø	mm	2.2					
Sheath Thickness	mm	1.6					
Cable Diameter – Ø	mm	6.0					
Cable Weight	kg / km	32				33	
MIT (Maximum Installation Tension)	N	150					
MAT (Maximum Allowable Tension)	N	1200					
Breaking Load	N	1350 – 2000					
Minimum Setting Diameter	mm	120					
Temperature Range	°C	Transport & Storage: -40 → +70		Installation: -20 → +45		Operation: -20 → +60	

CasaLink Block Terminal (CBT) Drop Cables

Cable Design – TC06051

DESIGN & CONSTRUCTION

- Optical fibre:** Single mode G.657.A1.
- Strength member:** 3 x 0.32mm brass plated steel wires.
- Tube:** Thermoplastic material, containing between 1 and 12 single-mode optical fibres and filled with a suitable water tightness compound.
- Longitudinal Water Tightness:** Water swellable elements (dry core only).
- Outer Sheath:** HDPE, 2 Ripcords beneath the sheath.
- Grooves/strips:** Indicate planes for easy sheath removal



The design above shows 12 fibre, the drop cable only contains 1 fibre.

Cable description

This loose tube optical drop cable is design for aerial and/or duct applications and is suitable for use under 11kV power cables. The cable has a break load of 1800N and a maximum aerial span length of 95M. The table below shows the ice and wind loading for this cable. The cable also has Openreach PIA approval, when using specified clamps as per page 1.

Layout		Single central tube	
Loose Tube Ø	mm	2.2	
Strength member	mm	3 x 0.32mm brass plated steel wires	
Sheath thickness	mm	1.6	
Cable Diameter	mm	6.0	
Cable Weight	kg / km	32	
Max installation tension	N	1200	
Maximum breaking load	N	1800	
Min. setting diameter	mm	120	
Temperature range	° C	Installation -20 -> +60	Operation -20 -> +60

Span (mts)	Temp	Wind and Ice Conditions							
		80 km 5 mm	100 km 5 mm	80 km 10 mm	120 km 5 mm	100 km 10 mm	80 km 15 mm	120 km 10 mm	100 km 15 mm
15	-30	Green							
25	-30	Green						Red	
35	-30	Green				Red			
45	-30	Green			Red				
55	-30	Green		Red					
65	-30	Green	Red						
75	-30	Green	Red						
85	-30	Green	Red						
95	-30	Green	Red						

CasaLink Block Terminal (CBT) Drop Cables

Prysmian

A Brand of Prysmian Group

Part Numbers for CBT Drops using cable TC06051

Single end terminated

Part Number	Length
XPCSC01745	10M
XPCSC01138	20M
XPCSC01156	22M
XPCSC01139	25M
XPCSC01140	30M
XPCSC01157	33M
XPCSC01141	35M
XPCSC01142	40M
XPCSC01143	45M
XPCSC01144	50M
XPCSC01158	55M
XPCSC01214	65M
XPCSC01459	80M
XPCSC01215	105M
XPCSC01460	120M
XPCSC01159	160M
XPCSC01746	250M
XPCSC01680	350M

CasaLink Block Terminal (CBT) Drop Cables

Prysmian

A Brand of Prysmian Group

Part Numbers for CBT Drops using cable TC06051

Terminated both ends

Part Number	Length
XPCSC01179	20M
XPCSC01180	40M
XPCSC01181	80M
XPCSC01182	120M
XPCSC01183	160M

Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2022, All Rights Reserved.
The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.